


Fall 2010/Spring 2011: Board Level Electronics Product Highlights



www.struck.de



Dear customer and dear probable customer. With this 2nd release in 2010 we are proud to show a card from the preseries batch of the SIS8300 digitizer according to the μ TCA for Physics draft standard. Generic and custom firmware development for the card is well under way.

Our Product Range

- VME Interfaces/Bus Couplers/Digital I/O
- VME Digitizers/ADCs
- μ TCA for Physics Digitizers/ADCs
- USB2.0 and Ethernet Based Electronics
- PCI Express Cards
- Custom Designs



Application Examples

- Gamma Spectroscopy
- Accelerator Controls
- Synchrotron Radiation
- Neutron Scattering
- Jet Plane Cabin Electronics Testing
- VME Board Development/Testing

Distributors

Australia

Scientific Devices Pty. Ltd.
Anders Agtoft
118 Atkinson Street / PO Box 163
Oakleigh MDC, Vic 3166

Phone: ++61 3 9569 1366
Fax: ++61 3 9563 4728

email: aagtoft@scientific-devices.com.au

China

Clover Technology Group, Inc.
Dahai Qi
No. 56A S. St.ZhongGuanCun,
FangYuan Mansion, Suite B0201
Beijing 100044, P.R. China

Phone: ++86 10 88026852-6855
Fax: ++86 25 8479 8787
email: dahai@clovertek.com

France

Acquitek
Philippe Vannier
1 bis rue Marcel Paul
91300 Massy, France

Phone: ++33 1 60 13 52 73
Fax: ++33 1 60 13 03 68

email: philippe.vannier@acquitek.com

India

AdvanceTech Controls Pvt. Ltd.
Pradim Kulkarni
507, sagar Tech Plaza, Saki Naka Junction,
Andheri Kurla Road
Andheri(East), Mumbai-400 072
Phone: ++91 22 66980434;
Fax: ++91 22 66980433

email: pradipk@advancetech.in

Japan

REPIC
Shigeru Morinaga
28-3 Kita Otsuka 1-chome
Toshima-ku, Tokyo 170-0004, Japan

Phone: ++81 33918 5326
Fax: ++81 33918 5712

email: sales@repic.co.jp

Korea

J-Tech, Inc.
J. D. Kim
Room #202, Semyeong BLDG.
224-2, Dongchung-1-Dong, Yeonsu-Ku,
Incheon 406-131, Korea

Phone: ++82 32 811 0883
Fax: ++82 32 811 0884
email: jindookim@netsgo.com

USA

Drivesoft LLC
Michael Doebelin
1655 Murfreesboro Rd., Suite A
Old Hickory, TN 37217

Phone: (615) 758 3718
Fax: (615) 758 3973
email: mdoebelin@drivesoft.com



Table of Contents

Distributors	2
VME Interfaces/Bus Couplers	4
SIS3150 USB2.0 to VME Interface	4
SIS1100/310x PCI/PCI Express/cPCI/AMC to VME Interface Family	5
VME Digital I/O	6
SIS3820 Multi Purpose Scaler/Digital VME I/O Card	6
SIS98xx VME64x Transition Boards	7
SIS9820 Optical and TTL Output Card	7
SIS9821 32 Channel Input Card	7
VME Digitizers	8
VME Digitizer Overview Table	8
SIS330x 8 Channel 100 MS/s 12/14-bit VME Digitizers	8
SIS3302 8 Channel 100 MS/s 16-bit VME Digitizer	9
SIS3302 User Interface Examples	10
SIS3302 Software Examples	11
SIS3320-250 8 Channel 250 MS/s 12-bit VME Digitizer	12
SIS3350 4 Channel 500 MS/s 12-bit VME Digitizer	13
SIS3305 8 Channel 1.25 GS/s 10-bit VME Digitizer	14
Miscellaneous	15
SIS3150 Dual TigerSHARC Twin CMC Carrier	15
SIS9300/992x/9930 CMC Mezzanines for SIS3150	15
SIS9965 USB2.0 Based Digital I/O Card With FPGA	16
SIS9967 USB2.0 16-channel 50 MS/s 14-bit Digitizer	16
FADCRMON Dual 12-bit 250 MS/s Digitizer With Ethernet Connectivity	17
SIS1104 4-Lane PCI Express Quad Optical Link Card	17
μTCA for Physics	18
SIS8300 10 channel 16-bit 125 MS/s μTCA for Physics Digitizer	18
μTCA/Simple μTCA Systems	19
μTCA/AdvancedMC	20
SIS8100 AMC GBit Link Card/VITA 57 FMC Carrier	20

VME Interfaces/Bus Couplers

SIS3150 USB2.0 to VME Interface


The SIS3150-USB is a high performance USB to VME interface. Connected to a USB2.0 port it supports block transfer speeds in excess of 30 MByte/s. USB1.1 operation is supported also. With the TigerSHARC DSP option it is perfectly suited for hard realtime applications and furnishes 650 ns single cycle access time.

Functionality

- 2 LEMO control inputs and outputs
- front panel diagnostic LEDs
- one or two TigerSHARC DSP option
- 64 MByte SDRAM w. DSP option
- VME master A16/A24/A32 D8/D16/D32/BLT32/MBLT64
- VME slave A32 D32/BLT32/MBLT64
- one available CMC site
- P2 access to lower CMC site
- Windows 2K/XP/Vista/7 and LINUX support
- Labwindows CVI/Labview/Matlab support
- KineticaRT support





SIS3150USB



Labwindows CVI Graphical User Interface of SIS3150 base program

Labview Examples:
Find and Initialize VI
Block Diagram of Block Read



SIS1100/310x PCI/PCI Express/cPCI/AMC to VME Interface Family

This optical link based PCI/cPCI/PCIe to VME interface card family covers demanding VME data acquisition applications as well as the small laboratory test bench setup. VME readout speeds in excess of 160 MBytes/s are measured in a realistic SST VME master slave setup (SIS3350 ADC as VME slave e.g.). Windows and LINUX drivers in combination with example and user interface code facilitate the migration from other platforms and system integration.



SIS1100e/3104

Common Functionality

- 6U single slot form factor on VME side
- 128 entry mapping table
- VME master A16/A24/A32/D8/D16/D32/BLT32
MBLT64/2eMBLT64
- block transfer address auto increment on/off (for FIFO reads)
- system controller function (to be disabled by jumper)
- up to 450 m link distance

Additional SIS3104 features

- SST implementation
- two front panel in- and outputs

Software Support

- Windows 2K/XP/Vista/7
- LINUX Kernel 2.6
- NI Labview/Labwindows
- VisualC++

Interface to	Interface Board	VME Board	Block Transfer Performance
PCI	SIS1100-uCMC/SIS1100-OPT	SIS3100/SIS3104	80 MByte/s
Compact PCI	SIS1100-cCMC/SIS1100-OPT	SIS3100/SIS3104	80 MByte/s
PCI Express	SIS1100-eCMC	SIS3100/SIS3104	80/160 MByte/s
μ TCA/AMC	SIS8100	SIS3100/SIS3104	80/160 MByte/s
USB	-	SIS3150USB	30 MByte/s

VME Interface Overview

The SIS1100/3100 is a co-operative Forschungszentrum Jülich/Struck development. SIS1100-uCMC and SIS1100-cCMC are produced under FZ-Jülich Lizenzvertrag 27

VME Digital I/O

SIS3820 Multi Purpose Scaler/Digital VME I/O Card

The module is a flexible FPGA based 6U VME board that allows for the implementation of a variety of digital I/O designs. Examples for off the shelf firmware designs are the 32 channel 200 MHz SIS3820-scaler and the 16 channel in/16 channel out SIS3820-latch designs.


Functionality

- 4 control inputs
- 4 control outputs
- 32 input/output channels + 32 I/Os on P2
- 32 channel 200 MHz scaler/counter implementation
- on board histogramming functionality
- TTL/ECL/NIM/LVDS and other logic level options
- 64/512 MByte SDRAM options
- flat cable, coax. connector and mixed options
- in field firmware upgrade
- A32/D32/BLT32/MBLT64/2eVME
- 80 MBytes/s with SIS1100/3100 in 2e VME
- Windows and LINUX software support for SIS1100/310x interfaces



SIS3820
LEMO and mixed

Design	Functionality
SIS3820	32 Channel Multi Purpose Scaler
SIS3820-Clock	Clock Distributor for Digitizers
SIS3820-3600	32-bit Latch w. Counter
SIS3820-3601	16 In/16 Out Register w. 4 Scalers and 4 Flipflops
SIS3820-1500	16 In/48 Out w. Pulse Generators
SIS3820 Firmware Implementations	



SIS3820
Read counters
Labview VI
(in 25 MHz test
pulse mode)



SIS3820 Connector Options

Version	Control I/O	Channels 1-16	Channels 1-16
LEMO	LEMO	LEMO	LEMO
Flat Cable	Flat Cable	Flat Cable	Flat Cable
Mixed	LEMO	Flat Cable	Flat Cable
Mixed	LEMO	LEMO	Flat Cable
Mixed	Flat Cable	LEMO	Flat Cable

Table of SIS3820 Connector Options

SIS98xx VME64x Transition Boards

SIS9820 Optical and TTL Output Card

The SIS3820 board has two times 16 I/O lines that are routed from the frontend FPGAs to the P2 connector. They can be accessed by means of VME64x transition cards. An example of a custom design for an accelerator control system is the SIS9820 board.

The SIS9820-V1 (shown to the right) features:

- DC/DC converters to supply +15/-15 V to external hardware
- two 15-pin DSUB connectors with 12 TTL outputs each
- 3 optical outputs with ST connectors

The SIS9820-V2 features:

- additional 4th optical output
- TTL LEMO outputs to monitor optical outputs



SIS9820




SIS9821 32 Channel Input Card

The SIS9821 board feeds 32 signals to the two times 16 I/O lines of the SIS3820 card. In combination with the corresponding firmware it expands the SIS3820 to a 64 channel scaler or 64-bit input register/latch.

The SIS9821 features:

- DC/DC converter to supply negative voltage for NIM/ECL configurations
- power LED
- TTL/ECL/NIM/LVDS and other logic level options
- flat cable, coax. connector and mixed options
- same configuration options as SIS3820 input channels



SIS9821

Feel free to inquire about custom SIS98xx designs

VME Digitizers

VME Digitizer Overview Table

Module	Sampling Speed	Channels	Resolution	Memory
SIS3305	5 GS/s	2	10-bit	512 MSample/channel
SIS3305	2.5 GS/s	4	10-bit	256 MSample/channel
SIS3305	1.25 GS/s	8	10-bit	128 MSample/channel
SIS3350	500 MS/s	4	12-bit	128 MSample/channel
SIS3320-250	250 MS/s	8	12-bit	32 MSample/channel
SIS3302	100 MS/s	8	16-bit	32 MSample/channel
SIS3302-4	100 MS/s	4	16-bit	32 MSample/channel
SIS3301	100 MS/s	8	14-bit	2 x 128 KSample/channel
SIS3300	100 MS/s	8	12-bit	2 x 128 KSample/channel

VME Digitizer Overview

Typical Common Properties

- Flexible input range configuration
- Single ended and differential inputs on units up to 250 MS/s, single ended on higher sampling speed boards
- Standard analog bandwidth up to Nyquist frequency, reduced or higher bandwidth on request

SIS330x 8 Channel 100 MS/s 12/14-bit VME Digitizers

The SIS3300/1 is an 8 channel 6U VME digitizer/transient recorder with a sampling rate of up to 105 MS/s and 12-bit (14-bit respective) resolution. The board has a width of one VME slot. The use of FPGAs for data handling and implementation of the VME interface allows for maximum flexibility. Acquisition into one memory bank in parallel to readout from the second memory bank in combination with a high speed slave interface allow for the implementation of demanding applications.

Functionality

- 8 channels with 12-bit/14-bit resolution
- 1 to 105 (15 to 105 respective) MSample/s per channel
- random clock mode for slower acquisition
- > 80 MHz analog bandwidth
- internal/external clock
- 2 x 128 KSamples/channel
- multi event mode
- event directory
- autostart capability
- pre/post trigger capability
- start/stop/gate inputs
- trigger output

interrupt capability

- A32/D32/BLT32/MBLT64/2eVME
- 80 MByte/s with SIS1100/3100 in 2e VME
- single ended/differential input options
- various input range options
- Windows/LINUX software support for SIS1100/310x interfaces

Custom Firmware Examples

- Medical Imaging
- Amanda Neutrino Detector
- Liquid Argon/Xenon WIMP



SIS3301

SIS3302 8 Channel 100 MS/s 16-bit VME Digitizer

The SIS3302 is our highest resolution digitizer. It embraces high dynamic range measurements as well as high resolution semiconductor spectroscopy and many other applications. A SIS3302 with Gamma firmware harnessing the Multi Channel Analyzer (MCA) implementation is perfectly suited to acquire spectra at synchrotron beamlines in conjunction with a SIS3820 in Multi Channel Scaler (MCS) mode of operation e.g..

Functionality

- 4/8 channels with 16-bit resolution
- 1 - 100 MSamples/s per channel
- random clock mode for slower acquisition
- > 50 MHz analog bandwidth
- 32 MSamples/channel memory
- programmable offset (DACs)
- internal/external clock
- trigger input and output
- refer to the table below for available input configuration options
- flexible acquisition and readout features
- firmware discriminator
- A32/D32/BLT32/MBLT64/2eVME
- generic and application specific firmware designs (see table below)
- custom firmware development support
- in field JTAG and VME firmware upgrade




SIS3302 and
SIS3302-4

Configuration	Connector Type(s)
Single Ended LEMO	8 x LEMO EPL.00.250.NTN
Single Ended SMA	8 x Telegärtner J01151A0201
Differential 00	8 x LEMO EGG.00.302.CLL
Differential 0S	8 x LEMO EPL.0S.302.HLN
Mixed	4 x EPL.00.250.NTN 4 x LEMO EPL.0S.302.HLN
SIS3302 Input Configurations	

Major/Minor Firmware Id.	Functionality
0x01 yy	8 Channel Generic Digitizer
0x14 0y	8 Channel Gamma with MCA
0x14 4y	4 Channel Gamma with MCA
0x31 yy	8 Channel Neutron/Gamma
SIS3302 Firmware Implementations	

SIS3302 User Interface Examples



SIS3302 Labwindows CVI
Gamma GUI with raw signal
and energy filter value screens

Co 60 spectrum acquired with Gamma firmware
(Courtesy of GSI Darmstadt)

Example screenshots from SIS3302 Gamma Matlab GUI

Figure 4: Energy Pulse Invert Parameters

	ADC 1	ADC 2	ADC 3	ADC 4	ADC 5	ADC 6	ADC 7	ADC 8
Module 1	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Module 2	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Module 3	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 4	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 5	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 6	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 7	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 8	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 9	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 10	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 11	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 12	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 13	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Module 14	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Figure 5: Define Common Sampling and Energy Parameters

Sampling Data Format Parameters

- Pretrigger Delay: 34
- Raw Data Sample Start Index: 1
- Raw Data Sample Length: 128
- Full Energy Trapezoidal (512 values)...
- Energy Data Sample Start Index 1
- Energy Data Sample Start Index 2
- Energy Data Sample Start Index 3
- Energy Data Sample Length

Energy Filter Parameters

- Decimation: disable
- Trapez Peaking Time: 175
- Trapez Gap: 40
- Energy Active Window Length: 0
- Trigger In Window Length: 0


SIS3302 Software Examples

Memory bank change with VME broadcast (Gamma firmware)

```
if (bank1_armed_flag == 1) {
    addr = gl_uint_SIS3302_BroadcastAddrConf +
           SIS3302_KEY_DISARM_AND_ARM_BANK2 ;
    bank1_armed_flag = 0; // bank 2 is armed
}
else {
    addr = gl_uint_SIS3302_BroadcastAddrConf +
           SIS3302_KEY_DISARM_AND_ARM_BANK1 ;
    bank1_armed_flag = 1; // bank 1 is armed
}
if ((error = sub_vme_A32D32_write(addr,0x0)) != 0) {
    sisVME_ErrorHandling (error, addr, "sub_vme_A32D32_write");
    gl_uint_system_status = SYSTEM_STATUS_MODULES_NOT_READY ;
    return -1 ;
}
```

Set address threshold in Matlab

```
% data for address threshold flag
data = address_threshold_value;
% set address threshold in loop
for module_index=1:gl_uint_NoOfModulesRun
    disp(module_index);
    addr = gl_uint_ModAddrRun(module_index) +
           SIS3302_END_ADDRESS_THRESHOLD_ALL_ADC ;
    a=calllib('sis3150usb_vme_win','sub_vme_A32D32_write',addr,data);
    if (a~=0)
        disp('error on setting address threshold');
    end
end
```



SIS3302 setup with
SIS3820 Clock distrib-
utor, SIS3820 trigger
distributor and SIS3150
USB to VME interface
(Courtesy University of Wiscon-
sin)



SIS3320-250 8 Channel 250 MS/s 12-bit VME Digitizer




SIS3320-250

The SIS3320-250 is the high speed version of the SIS3302 digitizer. Both cards have the same architecture in common. The SIS3320-250 is typically used in accelerator controls, Neutron/Gamma discrimination setups and other high speed applications.

Functionality

- 8 channels with 12-bit resolution
- 40 - 250 MSample/s per channel
- > 125 MHz analog bandwidth
- 32 MSample/channel memory
- random clock mode for slower acquisition
- programmable offset DACs
- internal/external clock
- trigger input and output
- flexible acquisition and readout features
- readout in parallel to acquisition
- A32/D32/BLT32/MBLT64/2eVME
- generic and application specific firmware designs (see table below)
- LEMO 00 or LEMO 0S connectors (SMA on request)
- firmware discriminator (8 individual thresholds)
- In field JTAG and VME firmware upgrade

SIS3320 Labwindows
CVI Neutron/Gamma
GUI with signal connected to 5 channels



Major Firmware Id.	Functionality
0x20	8 Channel Generic Digitizer
0x2A	8 Channel Neutron/Gamma
0x31	8 Channel with Accumulators
SIS3320-250 Firmware Implementations	

SIS3350 4 Channel 500 MS/s 12-bit VME Digitizer



The SIS3350 is a 4 channel 6U VME digitizer/transient recorder with a sampling rate of up to 500 MS/s per channel and 12-bit resolution. The board has a width of one VME slot. The use of FPGAs for data handling and implementation of the VME interface allows for maximum flexibility. The programmable input stage makes the SIS3350 the card of the choice for flexible lab and test beam setups.

Functionality

- 4 channels
- 12-bit resolution
- 1 to 500 MSample/s per channel
- > 250 MHz analog bandwidth
- internal clock
- external clock with variable threshold
- programmable offset (DACs)
- programmable gain (VGAs)
- 128 MSample/channel memory (512 MSample option)
- multi event mode
- event directory
- autostart capability
- pre/post trigger capability
- 2/4/8/16/32/64/128 sample averaging mode
- trigger generation/output
- additional LVDS in-/outputs
- BNC connectors
- single width 6U VME card
- A32/D32/BLT32/MBLT64/2eVME/SST
- 1/2/4 GBit optical link (SFF LC) option
- 10/100/1000 MBit Ethernet option



SIS3350



Gain and offset screen of SIS3350 base program Labwindows CVI GUI

Main screen of SIS3350 base program Labwindows CVI GUI



new

SIS3305 8 Channel 1.25 GS/s 10-bit VME Digitizer

2/4/8 Channel 5/2.5/1.25 GS/s

The SIS3305 is a dual quad channel ADC chip based digitizer/transient recorder with 10-bit resolution. The four by four cross point switch ADC technology allows for two channel 5 GS/s, four channel 2.5 GS/s and eight channel 1.25 GS/s operation. Xilinx Virtex 5 frontend FPGAs in combination with a Virtex 4 VME interface implementation allow for maximum data handling flexibility.

Functionality

- single width 6U VME card
- 2/4/8 channels
- 5 GS/s, 2.5 GS/s or 1.25 GS/s per channel
- 10-bit resolution
- 512/256/128 MSamples/channel memory
- 2 GHz analog bandwidth
- 4 channel input stage piggy boards
- SMA connectors for analog inputs
- internal/External clock
- readout in parallel to acquisition
- multi event mode
- individual trigger thresholds
- channel above threshold LEDs
- pre/post trigger capability
- sparsification
- A32/D32/BLT32/MBLT64/2eVME/SST
- in field JTAG and VME firmware upgrade capability



SIS3305

Front Panel Control Signals:

- differential clock output
- differential clock input
- trigger OR output/trigger input
- counter input
- reset counter/time Stamp input
- 1/2/4 GBit/s optical link option
- veto input option



16 Channel 1.25 GS/s SIS3305 System



Miscellaneous

SIS3150 Dual TigerSHARC Twin CMC Carrier

The SIS3150 is a versatile building block for VME based data acquisition systems. It combines substantial DSP computing power with a high speed VME master/slave implementation and the modular mezzanine (CMC, IEEE 1386) concept.

Functionality

- VME A32 D32/BLT32/MBLT64/2eVME (others on request)
- 2 CMC sites
- up to 2 TigerSHARC signal processors (clocked at 250 MHz)
- 64 MBytes SDRAM (requires TigerSHARC memory controller)
- FLASH memory
- front panel I/O option
 - 2 LEMO inputs and 2 LEMO outputs
- P2 I/O option
 - 16 single ended or 8 differential inputs per CMC
 - 16 single ended or 8 differential outputs per CMC
- interrupt capability
- hot swap (in VME64 environments)




SIS3150 with 2 DSPs

SIS9300/992x/9930 CMC Mezzanines for SIS3150

The CMC mezzanine approach in combination with direct access to FPGA or DSP resources -i.e. without involved PCI or PCI Express bridges- allows for the implementation of high performance frontend interface cards with moderate glue logic design effort. A range of Struck CMCs was developed over the last couple of years in the context of different projects.

This successful approach was adopted by the VITA 57 FMC (FPGA Mezzanine Card) standard more recently.

Related product: SIS8100 FMC carrier, see page 16.



SIS9300 and 992x/9930 CMCs

Module	Functionality	Application Example
SIS9300	4 Channel 100 MS/s 14-bit Digitizer	Germanium Detector Readout
SIS9920	Ethernet Interface	Jet Plane Cabin Electronics Testing
SIS9921-RS485	RS485 Interface	Optical Sensor Head Readout
SIS9921-USB	USB Interface	SIS3150USB Interface
SIS9922	RS485 Interface With Relais	Jet Plane Cabin Electronics Testing
SIS9930	Digital I/O	RSIS Grinder Inspection System

Available CMC Mezzanines

Feel free to inquire about a custom CMC development for your application

SIS9965 USB2.0 Based Digital I/O Card With FPGA

The SIS9965 is a single Euro form factor FPGA board with USB2.0 communication interface.

Functionality

- C-rail/standalone mount
- USB2.0
- 8 channels of 24V digital inputs (opto-decoupled)
- 8 channels of 24V digital outputs (opto-decoupled)
- 4 channels of TTL inputs (high impedance)
- 4 channels of TTL Outputs (standard TTL)
- 4 channels of TTL 50 Ohm inputs
- 4 channels of TTL 50 Ohm outputs
- 4 channels of RS422 inputs A+/A-, B+/B-, Z+/Z-, Reserve+/- (opto-decoupled)
- one channel RS422 output (e.g. Clock Out) (opto-decoupled)
- Xilinx FPGA
- +5V supply, +24V depending on external circuitry
- in field JTAG firmware upgrade capability



SIS9965
mounted in DIN rail fixture

Application Example:
Shaft encoder clock multiplier/divider in
aluminum rolling mill instrumentation

SIS9967 USB2.0 16-channel 50 MS/s 14-bit Digitizer

The SIS9967 is a standalone 16 channel 14-bit digitizer card with USB2.0 and optical link readout capabilities. Two 125 MS/s 12-bit DAC channels allow for control of external hardware and/or implementation of fast feedback systems. The card can be used in a desktop enclosure with a 15-19.5V laptop power supply or integrated into a wall mount installation.

Functionality

- double Euro form factor
- 16 channels
- 50 MS/s per channel
- 14-bit resolution
- USB2.0 or optical link connection
- 2 channels 125 MS/s 12-bit DAC
- internal/external clock
- clock output
- 8-bit digital input
- 5-bit digital output
- 8 RS422/485 serial I/Os
- servo motor control
- 15-19.5 V supply voltage
- Xilinx Virtex IV FPGA
- in field JTAG and VME firmware upgrade capability



SIS9967 with
Optical Link
Medium



Application Laser Scanner

FADCRMON Dual 12-bit 250 MS/s Digitizer With Ethernet Connectivity

The FADCRMON digitizer board with Ethernet was originally developed for the DESY PANDORA (Photon And Neutron DOse Rate meter). The PANDORA systems are used in radiation protection applications with conventional and pulsed radiation fields like Petra III or FLASH. Complete systems will be available through Berthold Technologies.



FADCRMON

Functionality

- 4 channels of 250 MS/s 12-bit digitizer
- one LEMO TTL input (for scaler applications e.g.)
- 4 TTL inputs
- 2 digital outputs
- Xilinx Virtex 4 based
- Virtex 4 PPC for computing tasks
- 10/100/1000 Ethernet
- 1/2/4 GBit/s SFF link medium option
- DDR2, Flash and EEPROM memory

- diagnostic LEDs
- 2 test push buttons
- application software update over Ethernet
- in field firmware update

Application Examples

- distributed digitizer systems
- standalone digitizer with data processing

Contract Development for DESY
Production under DESY license LV 58

SIS1104 4-Lane PCI Express Quad Optical Link Card

Multiple lane PCI Express cards allow for the implementation of data acquisition hardware with unprecedented performance. The SIS1104 was developed for the readout of data streams from pn-CCD pixel detectors at state of the art X-ray sources like the DESY FLASH. One of the key requirements is loss free high sustained data throughput.



SIS1104

Functionality

- 4-Lane PCI Express
- Xilinx Virtex 5 based
- four 1/2/4 GBit/s SFF link media
- 640 MByte/s sustained throughput with LINUX driver
- 2 GByte buffer memory option

Application examples

- pixel detector readout systems
- frontend data stream receiver
- point to point readout of SIS3305 and SIS3350 digitizer boards

The SIS1104 was developed under contract for the Halbleiterlabor of the Max Planck Gesellschaft

new

μTCA for Physics *

SIS8300 10 channel 16-bit 125 MS/s

μTCA for Physics Digitizer

ATCA and its substandards like μTCA play an increasingly important role in the embedded world. Efforts of the PICMG workgroup xTCA for Physics to optimize the standard for next generation accelerators and experiments are well under way. The SIS8300 digitizer -under development for applications at the European XFEL e.g.- can be regarded as a demonstrator for the new standard.

Functionality

- 4 lane PCI Express connectivity
- 10 channels 125 MS/s 16-bit ADC
- 10 MS/s to 125 MS/s per channel sampling speed
- XC5VLX50T-3FFG1136C Xilinx
- 25 MSample buffer memory per channel
- AC and DC input stage
- ADC inputs through Rear Transition Module (RTM)
- internal, front panel, RTM and backplane clock sources
- two 16-bit DACs for fast feedback implementation
- high precision clock distribution circuitry
- programmable delay of dual channel digitizer groups
- Gigabit link port implementation to backplane
- twin SFP card cage for high speed system interconnects



Related μTCA Products	Page
SIS8100/3104 μTCA to VME Interface	5
SIS8100 μTCA FMC Carrier	20
SIS8100 μTCA Gigabit Link Card	20

New Development in co-operation with DESY under ZIM Förderkennzeichen 2460101MS9

* It is PICMG's policy to prohibit claims of compliance with respect to a specification under development. Any such claims must be understood as applying to a draft, which is subject to change.

µTCA/AdvancedMC

SIS8100 AMC GBit Link Card/VITA 57 FMC Carrier

The SIS8100 is a single width/mid-height AdvancedMC module with single lane PCI Express functionality (AMC.1). The first function is to extend our optical Link family into the xTCA world. The second stuffing option is the single VITA 57 FMC carrier, with target applications like fast I/O.

Functionality

- AMC.1 AdvancedMC
- single width/mid-height
- PEX8311 PCI Express to local bus bridge chip
- Atmega128 based management
- Xilinx FX20 Virtex 4
- 1/2/4 GBit/s SFF link medium option or
- single FMC carrier option

Applications


- SIS8100/3104 µTCA to VME interface
- frontend data stream receiver
- digital I/O with FMC mezzanine
- analog I/O with FMC mezzanine



SIS8100 In Gigabit Link Configuration

Software Support

- Windows 2K/XP/Vista/7
- LINUX Kernel 2.6
- NI Labview/Labwindows
- VisualC++



SIS8100 Block Diagram

photographs: www.iStockphoto.com and struck
front page XFEL cavity illustration courtesy of DESY

Struck Innovative Systeme GmbH
 Harksheider Str. 102A
 22399 Hamburg
 Germany
 email: info@struck.de
 web: www.struck.de
 phone: ++49 40 60 87 305 0
 fax: ++49 40 60 87 305 20

